


TRPM8 Antibody (C-term C940)

Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP8181d	WB, IHC, E	H	Q7Z2W7
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB14420

Application Data:

Calculated MW: 127685 Da



Western blot analysis of TRPM8 (arrow) using rabbit polyclonal TRPM8 Antibody (C-term C940)(Cat.#AP8181d).293 cell lysates (2 ug/lane) either nontransfected (Lane 1) or transiently transfected with the TRPM8 gene (Lane 2) (Origene Technologies).



Formalin-fixed and paraffin-embedded human prostate carcinoma tissue reacted with TRPM8 antibody (C-term C940) (Cat.#AP8181d), which was peroxidase-conjugated to the secondary antibody, followed by DAB staining. This data demonstrates the use of this antibody for immunohistochemistry; clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
79054	TRPM8

Other Names:

Transient receptor potential cation channel subfamily M member 8; Long transient receptor potential channel 6; LTrpC6; Transient receptor potential-p8; Trp-p8; TRPM8

Target/Specificity:

This TRPM8 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 933~963 amino acids from the C-term(C940) of human TRPM8.

Application Notes:

The suggested dilution is:

ELISA 1:1,000
Western blotting 1:50~100
Immunohistochemistry 1:10~50

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is prepared by Saturated Ammonium Sulfate (SAS) precipitation followed by dialysis against PBS.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

TRPM8 Antibody (C-term C940) is for research use only and not for use in diagnostic or therapeutic procedures.
