


## HNF4A Antibody (N-term)

### Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP9435a	WB, IF, E	H	<a href="#">P41235</a>

Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB17744

#### Application Data: Calculated MW: 52785 Da



Western blot analysis of HNF4A Antibody (N-term) (Cat. #AP9435a) in 293 cell line lysates (35ug/lane). HNF4A (arrow) was detected using the purified Pab.



Confocal immunofluorescent analysis of HNF4A Antibody (N-term)(Cat#AP9435a) with MCF-7 cell followed by Alexa Fluor 488-conjugated goat anti-rabbit IgG (green). DAPI was used to stain the cell nuclear (blue).

Gene ID:	Gene Symbol:
<a href="#">3172</a>	HNF4A

#### Other Names:

Transcription factor 14, TCF-14; Nuclear receptor subfamily 2 group A member 1; Transcription factor HNF-4; Hepatocyte nuclear factor 4-alpha, HNF-4-alpha, TCF14, NR2A1, HNF4, HNF4A

#### Target/Specificity:

This HNF4A antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 116~145 amino acids from the N-terminal region of human HNF4A.

#### Application Notes:

The suggested dilution is:

ELISA 1:1,000  
Western blotting 1:50~100  
Immunofluorescence 1:10~50

---

**Format:**

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is prepared by Saturated Ammonium Sulfate (SAS) precipitation followed by dialysis against PBS.

---

**Storage:**

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

---

**Precautions:**

HNF4A Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.

---