

## SAFETY DATA SHEET

Revision Date 26-May-2017

Revision Number 2

### 1. Identification

**Product Name** 1-Octyl-3-methylimidazolium hexafluorophosphate

**Cat No. :** AC356760000; AC356760050; AC356760250

**Synonyms** None Known.

**Recommended Use** Laboratory chemicals.

**Uses advised against** Not for food, drug, pesticide or biocidal product use

#### Details of the supplier of the safety data sheet

##### Company

Fisher Scientific  
One Reagent Lane  
Fair Lawn, NJ 07410  
Tel: (201) 796-7100

Acros Organics  
One Reagent Lane  
Fair Lawn, NJ 07410

##### **Emergency Telephone Number**

For information **US** call: 001-800-ACROS-01 / **Europe** call: +32 14 57 52 11

Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99

**CHEMTREC** Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

### 2. Hazard(s) identification

#### Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin Corrosion/irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity (single exposure)	Category 3
Target Organs - Respiratory system.	

#### Label Elements

##### **Signal Word**

Warning

##### **Hazard Statements**

Causes skin irritation

Causes serious eye irritation

May cause respiratory irritation



**Precautionary Statements****Prevention**

Wash face, hands and any exposed skin thoroughly after handling  
Wear protective gloves/protective clothing/eye protection/face protection  
Avoid breathing dust/fume/gas/mist/vapors/spray  
Use only outdoors or in a well-ventilated area

**Inhalation**

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing  
Call a POISON CENTER or doctor/physician if you feel unwell

**Skin**

IF ON SKIN: Wash with plenty of soap and water  
If skin irritation occurs: Get medical advice/attention  
Take off contaminated clothing and wash before reuse

**Eyes**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
If eye irritation persists: Get medical advice/attention

**Storage**

Store in a well-ventilated place. Keep container tightly closed  
Store locked up

**Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

None identified

### 3. Composition / information on ingredients

Component	CAS-No	Weight %
1-Octyl-3-methylimidazolium hexafluorophosphate	304680-36-2	> 98

### 4. First-aid measures

<b>Eye Contact</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Obtain medical attention.
<b>Skin Contact</b>	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Obtain medical attention.
<b>Inhalation</b>	Remove from exposure, lie down. Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Obtain medical attention.
<b>Ingestion</b>	Clean mouth with water. Get medical attention.
<b>Most important symptoms/effects</b>	No information available.
<b>Notes to Physician</b>	Treat symptomatically

### 5. Fire-fighting measures

<b>Suitable Extinguishing Media</b>	Water spray. Carbon dioxide (CO <sub>2</sub> ). Dry chemical. Chemical foam.
<b>Unsuitable Extinguishing Media</b>	No information available
<b>Flash Point</b>	No information available
<b>Method -</b>	No information available
<b>Autoignition Temperature</b>	No information available
<b>Explosion Limits</b>	
<b>Upper</b>	No data available
<b>Lower</b>	No data available

**Sensitivity to Mechanical Impact** No information available  
**Sensitivity to Static Discharge** No information available

**Specific Hazards Arising from the Chemical**

Keep product and empty container away from heat and sources of ignition.

**Hazardous Combustion Products**

Hydrogen chloride gas Nitrogen oxides (NO<sub>x</sub>) Carbon monoxide (CO) Carbon dioxide (CO<sub>2</sub>)

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**NFPA**

**Health**  
2

**Flammability**  
0

**Instability**  
1

**Physical hazards**  
N/A

**6. Accidental release measures****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment.

**Environmental Precautions**

See Section 12 for additional ecological information.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal.

**7. Handling and storage****Handling**

Avoid contact with skin and eyes. Do not breathe dust. Do not breathe vapors or spray mist.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

**8. Exposure controls / personal protection****Exposure Guidelines**

This product does not contain any hazardous materials with occupational exposure limit established by the region specific regulatory bodies.

**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location.

**Personal Protective Equipment****Eye/face Protection**

Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.

**Skin and body protection**

Wear appropriate protective gloves and clothing to prevent skin exposure.

**Respiratory Protection**

Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN 149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

**Hygiene Measures**

Handle in accordance with good industrial hygiene and safety practice.

**9. Physical and chemical properties****Physical State**

Liquid

**Appearance**

Light yellow

**Odor**

No information available

**Odor Threshold**

No information available

**pH**

No information available

Melting Point/Range	No data available
Boiling Point/Range	No information available
Flash Point	No information available
Evaporation Rate	No information available
Flammability (solid,gas)	No information available
Flammability or explosive limits	
Upper	No data available
Lower	No data available
Vapor Pressure	No information available
Vapor Density	No information available
Specific Gravity	1.235
Solubility	No information available
Partition coefficient; n-octanol/water	No data available
Autoignition Temperature	No information available
Decomposition Temperature	No information available
Viscosity	No information available
Molecular Formula	C12 H23 N2 . P F6
Molecular Weight	340.29

## 10. Stability and reactivity

Reactive Hazard	None known, based on information available
Stability	Stable under normal conditions. Hygroscopic.
Conditions to Avoid	Exposure to moist air or water.
Incompatible Materials	Strong oxidizing agents
Hazardous Decomposition Products	Hydrogen chloride gas, Nitrogen oxides (NOx), Carbon monoxide (CO), Carbon dioxide (CO <sub>2</sub> )
Hazardous Polymerization	No information available.
Hazardous Reactions	None under normal processing.

## 11. Toxicological information

### Acute Toxicity

**Product Information** No acute toxicity information is available for this product

**Component Information**  
**Toxicologically Synergistic** No information available  
**Products**

### Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation	No information available
Sensitization	No information available
Carcinogenicity	The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS-No	IARC	NTP	ACGIH	OSHA	Mexico
1-Octyl-3-methylimidazolium hexafluorophosphate	304680-36-2	Not listed	Not listed	Not listed	Not listed	Not listed

**Mutagenic Effects** No information available

**Reproductive Effects** No information available.

**Developmental Effects** No information available.

<b>Teratogenicity</b>	No information available.
<b>STOT - single exposure</b>	Respiratory system
<b>STOT - repeated exposure</b>	None known
<b>Aspiration hazard</b>	No information available
<b>Symptoms / effects, both acute and delayed</b>	No information available
<b>Endocrine Disruptor Information</b>	No information available
<b>Other Adverse Effects</b>	The toxicological properties have not been fully investigated.

## 12. Ecological information

### Ecotoxicity

Do not empty into drains.

<b>Persistence and Degradability</b>	No information available
<b>Bioaccumulation/ Accumulation</b>	No information available.
<b>Mobility</b>	No information available.

## 13. Disposal considerations

<b>Waste Disposal Methods</b>	Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.
-------------------------------	---

## 14. Transport information

<b>DOT</b>	Not regulated
<b>TDG</b>	Not regulated
<b>IATA</b>	Not regulated
<b>IMDG/IMO</b>	Not regulated

## 15. Regulatory information

### International Inventories

#### Legend:

X - Listed

E - Indicates a substance that is the subject of a Section 5(e) Consent order under TSCA.

F - Indicates a substance that is the subject of a Section 5(f) Rule under TSCA.

N - Indicates a polymeric substance containing no free-radical initiator in its inventory name but is considered to cover the designated polymer made with any free-radical initiator regardless of the amount used.

P - Indicates a commenced PMN substance

R - Indicates a substance that is the subject of a Section 6 risk management rule under TSCA.

S - Indicates a substance that is identified in a proposed or final Significant New Use Rule

T - Indicates a substance that is the subject of a Section 4 test rule under TSCA.

XU - Indicates a substance exempt from reporting under the Inventory Update Rule, i.e. Partial Updating of the TSCA Inventory Data Base Production and Site Reports (40 CFR 710(B)).

Y1 - Indicates an exempt polymer that has a number-average molecular weight of 1,000 or greater.

Y2 - Indicates an exempt polymer that is a polyester and is made only from reactants included in a specified list of low concern reactants that comprises one of the eligibility criteria for the exemption rule.

### U.S. Federal Regulations

<b>TSCA 12(b)</b>	Not applicable
<b>SARA 313</b>	Not applicable

**SARA 311/312 Hazard Categories**

Acute Health Hazard	Yes
Chronic Health Hazard	No
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

**CWA (Clean Water Act)** Not applicable

**Clean Air Act** Not applicable

**OSHA** Occupational Safety and Health Administration  
Not applicable

**CERCLA**  
Not applicable

**California Proposition 65** This product does not contain any Proposition 65 chemicals

**U.S. State Right-to-Know Regulations** Not applicable

**U.S. Department of Transportation**

Reportable Quantity (RQ):	N
DOT Marine Pollutant	N
DOT Severe Marine Pollutant	N

**U.S. Department of Homeland Security**  
This product does not contain any DHS chemicals.

**Other International Regulations**

**Mexico - Grade** No information available

**16. Other information**

**Prepared By** Regulatory Affairs  
Thermo Fisher Scientific  
Email: EMSDS.RA@thermofisher.com

**Revision Date** 26-May-2017

**Print Date** 26-May-2017

**Revision Summary** This document has been updated to comply with the US OSHA HazCom 2012 Standard replacing the current legislation under 29 CFR 1910.1200 to align with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of SDS**