PRODUCT: EZSolution[™] DAPT


ALTERNATE NAME:

N-[N-(3,5-Difluorophenacetyl-L-alanyl)]-S-phenylglycine t-Butyl Ester

CATALOG #:

2663-5 5 mg

STRUCTURE:



432.46

 $C_{23}H_{26}F_2N_2O_4$

MOLECULAR FORMULA:

MOLECULAR WEIGHT:

CAS No. 208255-80-5

- APPEARANCE:LiquidFORMULATION:A 10 mM solution in anhydrous DMSOPURITY:≥98% by TLCSTORAGE:Store at -20°C. Protect from air and moisture
- DESCRIPTION:
 A 10 mM (5 mg in 1156 μl) solution of γ-secretase inhibitor

 DAPT (Cat. No.1855) in anhydrous DMSO.

RELATED PRODUCTS:

APP Antibody (Cat. No. 6001-100) Beta-Secretase, human recombinant (Cat. No. 7604-20, 100, 1000) Beta-Secretase Activity Assay Kit (Cat. No. K360-100) Beta Secretase Inhibitor I (Cat. No. 7501-1) Beta Secretase Inhibitor II (Cat. No. 7502-1) Compound 34 (Cat. No. 1898-200, 1000) Compound E (Cat. No. 1949-250, 1000) Compound W (Cat. No. 2208-50, 250) DAPT (Cat. No. 1855-5) DBZ (Cat. No. 2649-1,5) L-685, 258 (Cat. No. 1713-250 LY2886721 (Cat. No. 2399-5, 25) LY-411575 (Cat. No. 2648-1, 5) RO4929097 (Cat. No. 2011-1, 5) Semagacestat (Cat. No. 2430-1, 5) TACE Antibody (Cat. No. 3222-100)

HANDLING:

Do not take internally. Wear gloves and mask when handling the product! Avoid contact by all modes of exposure.

USAGE:

FOR RESEARCH USE ONLY! Not to be used in humans.