




Dimensions (Unit:mm)



VWR® 4 Well Tissue Culture Plates

Description: 4 Well, Non-Treated/ Treated, Sterilized

Purpose: Available in surface-treated or non-treated

Materials

Plate: GPPS (General polystyrene) Colour: Clear

Lid: GPPS (General polystyrene) Colour: Clear

Features

- 4-well plates have a pinchbar design, and flat-bottom round wells, with lid
- Lid with notched corners for good fit and easy orientation
- Temperature: -20°C~+50°C
- Sterilization: sterilized by gamma irradiation SAL10⁻⁶(ISO11137)
- Free of detectable DNase/RNase, human DNA and pyrogens, Contents non-cytotoxic
- Available in individual recyclable PET
- Autoclavability: No
- Assembled plate and lid height: 13.5 mm
- Max. volume (single well): 1.86 ml
- Working volume (single well): 1.0 ml
- Growth area (single well): 1.96 cm²
- Every product is printed with a batch number for traceability
- Shelf Life: 3 years after month of production

VWR® 4 Well Tissue Culture Plates

VWR EU Cat. No.	VWR NA Cat. No.	Description	Sterile	Qty/Tray	Qty/Pk	Qty/Case
732-2904	10813-630	Tissue Culture plates, General, Non-treated, 4 wells, sterile	Yes	1	50	100
732-2905	10814-222	Tissue Culture plates, Standard, Treated, 4 wells, sterile	Yes	1	50	100