



VWR® 6 Well Non-Treated Tissue Culture Plates

Description: 6 Well, Non-Treated, Sterilized
Purpose: For use in applications where cell attachment is not desired


Materials
Plate: GPPS (General polystyrene) Colour: Clear
Lid: GPPS (General polystyrene) Colour: Clear

- Features
- Temperature: -20°C~+50°C
 - Sterilisation: sterilized by gamma irradiation SAL10⁻⁶(ISO11137)
 - Non-pyrogenic
 - Available in individual recyclable PET
 - Autoclavability: No
 - Assembled plate and lid height: 22.2 mm
 - Max. volume (single well): 17.0 ml
 - Working volume (single well): 1.9~2.9 ml
 - Growth area (single well): 9.6 cm²
 - Every product is printed with a batch number for traceability
 - Shelf Life: 3 years after month of production



VWR® 6 Well Non-Treated Tissue Culture Plates


VWR EU Cat. No.	VWR NA Cat. No.	Description	Sterile	Qty/Tray	Qty/Pk	Qty/Case
734-2777	10861-554	6 Well Tissue Culture Plate, Non-treated, Sterilized	Yes	1	50	100




VWR® 12 Well Non-Treated Tissue Culture Plates

Description: 12 Well, Non-Treated, Sterilized
Purpose: For use in applications where cell attachment is not desired

Materials
Plate: GPPS (General polystyrene) Colour: Clear
Lid: GPPS (General polystyrene) Colour: Clear



- Features
- Temperature: -20°C~+50°C
 - Sterilization: sterilized by gamma irradiation SAL10⁻⁶(ISO11137)
 - Non-pyrogenic
 - Available in individual recyclable PET
 - Autoclavability: No
 - Assembled plate and lid height: 22.7 mm
 - Max. volume (single well): 6.8 ml
 - Working volume (single well): 0.76~1.14 ml
 - Growth area (single well): 3.85 cm²
 - Every product is printed with a batch number for traceability
 - Shelf Life: 3 years after month of production



VWR® 12 Well Non-Treated Tissue Culture Plates

VWR EU Cat. No.	VWR NA Cat. No.	Description	Sterile	Qty/Tray	Qty/Pk	Qty/Case
734-2778	10861-556	12 Well Tissue Culture Plate, Non-treated, Sterilized	Yes	1	50	100