

Heme Oxygenase-2 Polyclonal Antibody

CATALOG #:	3392-100
AMOUNT:	100 µg
LOT #:	_____
HOST:	Rabbit
IMMUNOGEN:	Synthetic peptide surrounding amino acid 34 of human HO-2 (Internal ID# BV-A2)
SPECIES REACTIVITY:	Human, Mouse, Rat, Hamster, Monkey

FORMULATION:

100 µg (0.5 mg/ml) affinity purified rabbit polyclonal antibody in phosphate-buffered saline (PBS) containing 30% glycerol, 0.5% BSA, and 0.01% thimerosal.

STORAGE CONDITIONS:

Store at -20°C. For long term storage, aliquot and freeze at -70°C. Avoid repeated freeze/thaw cycles.

BACKGROUND:


Heme oxygenase (HO) is a microsomal enzyme that oxidatively cleaves heme, a pro-oxidant, into carbon monoxide and biliverdin. Two heme oxygenase isozymes, termed HO-1 and HO-2, have been identified so far. At the amino acid level, HO-1 and HO-2 are 42% homologous. However, each isozyme is evolutionarily highly conserved. HO-1 is the inducible form of the enzyme and is therefore also referred to as stress protein Hsp32. Expression of HO-1 can be induced by a variety of stimuli such as heme, metals, hormones, UV radiation and sulfhydryl depleting agents. In contrast, HO-2 is the constitutive form of the enzyme. It is not inducible by exogenous stimuli and HO-2 is the most prevalent form in most tissues, except the spleen where HO-1 levels are predominant under normal conditions.

SPECIFICITY:

The antibody recognizes ~36 kDa Heme-Oxygenase-2 of human, mouse, rat, hamster, and monkey origins. Blocking peptide (Cat.# 3392BP-50) is available separately.

APPLICATION:

The antibody has been used in Western blotting (0.5-4 µg/ml). Per researcher's feedback, it can also be used in immunoprecipitation (20 µg/ml) and immunohistochemistry (20 µg/ml, frozen section tested). However, the optimal concentrations should be determined individually.



FOR RESEARCH USE ONLY! Not to be used on humans.

RELATED PRODUCTS:

Apoptosis Detection Kits & Reagents

- Annexin V Kits & Bulk Reagents
- Caspase Assay Kits & Reagents
- Mitochondrial Apoptosis Kits & Reagents
- Nuclear Apoptosis Kits & Reagents
- Apoptosis Inducers and Set
- Apoptosis siRNA Vectors

Cell Fractionation System

- Mitochondria/Cytosol Fractionation Kit
- Nuclear/Cytosol Fractionation Kit
- Membrane Protein Extraction Kit
- Cytosol/Particulate Rapid Separation Kit
- Mammalian Cell Extraction Kit
- FractionPREP Fractionation System

Cell Proliferation & Senescence

- Quick Cell Proliferation Assay Kit
- Senescence Detection Kit
- High Throughput Apoptosis/Cell Viability Assay Kits
- LDH-Cytotoxicity Assay Kit
- Bioluminescence Cytotoxicity Assay Kit
- Live/Dead Cell Staining Kit

Cell Damage & Repair

- HDAC Fluorometric & Colorimetric Assays & Drug Discovery Kits
- HAT Colorimetric Assay Kit & Reagents
- DNA Damage Quantification Kit
- Glutathione & Nitric Oxide Fluorometric & Colorimetric Assay Kits

Signal Transduction

- cAMP & cGMP Assay Kits
- Akt & JNK Activity Assay Kits
- Beta-Secretase Activity Assay Kit

Adipocyte & Lipid Transfer

- Recombinant Adiponectin, Survivin, & Leptin
- CETP Activity Assay & Drug Discovery Kits
- PLTP Activity Assay & Drug Discovery Kits
- Total Cholesterol Quantification Kit

Molecular Biology & Reporter Assays

- siRNA Vectors
- Cloning Insert Quick Screening Kit
- Mitochondrial & Genomic DNA Isolation Kits
- 5 Minutes DNA Ligation Kit
- 20 Minutes Gel Staining/Destaining Kit
- β -Galactosidase Staining Kit & Luciferase Reporter Assay Kit

Growth Factors and Cytokines

Monoclonal and Polyclonal Antibodies