

# SAFETY DATA SHEET

## 1. Identification

**Product identifier:** SODIUM THIOSULFATE PENTAHYDRATE

**Other means of identification**

**Product No.:** 7765, 3945, 3960, 3946, 8100, 7763

**Recommended use and restriction on use**

**Recommended use:** Not available.

**Restrictions on use:** Not known.

**Manufacturer/Importer/Supplier/Distributor Information**

**Manufacturer**

**Company Name:** Avantor Performance Materials, Inc.  
**Address:** 3477 Corporate Parkway, Suite 200  
Center Valley, PA 18034

**Telephone:** Customer Service: 855-282-6867

**Fax:**  
**Contact Person:** Environmental Health & Safety  
**e-mail:** info@avantormaterials.com

**Emergency telephone number:**

24 Hour Emergency: 908-859-2151

Chemtrec: 800-424-9300

## 2. Hazard(s) identification

**Hazard Classification**

Not classified

**Label Elements**

**Hazard Symbol:** No symbol

**Signal Word:** No signal word.

**Hazard Statement:** Not applicable

**Precautionary Statement** Not applicable

**Other hazards which do not result in GHS classification:**

None.

## 3. Composition/information on ingredients

**Substances**

**Composition Comments:** The components are not hazardous or are below required disclosure limits.

## 4. First-aid measures

<b>General information:</b>	Get medical advice/attention if you feel unwell. Show this safety data sheet to the doctor in attendance.
<b>Ingestion:</b>	Rinse mouth thoroughly. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Inhalation:</b>	Move to fresh air. Get medical attention if symptoms persist.
<b>Skin Contact:</b>	Wash skin thoroughly with soap and water. Get medical attention if irritation persists after washing.
<b>Eye contact:</b>	Flush thoroughly with water. If irritation occurs, get medical assistance.

**Most important symptoms/effects, acute and delayed**

**Symptoms:** May cause irritation to skin, eyes, and respiratory tract.

**Indication of immediate medical attention and special treatment needed**

**Treatment:** Treat symptomatically. Symptoms may be delayed.

**5. Fire-fighting measures**

**General Fire Hazards:** The product is non-combustible.

**Suitable (and unsuitable) extinguishing media**

**Suitable extinguishing media:** Use fire-extinguishing media appropriate for surrounding materials.

**Unsuitable extinguishing media:** None known.

**Specific hazards arising from the chemical:** During fire, gases hazardous to health may be formed.

**Special protective equipment and precautions for firefighters**

**Special fire fighting procedures:** Move containers from fire area if you can do so without risk. Use water spray to keep fire-exposed containers cool. Cool containers exposed to flames with water until well after the fire is out.

**Special protective equipment for fire-fighters:** Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

**6. Accidental release measures**

**Personal precautions, protective equipment and emergency procedures:** Keep unauthorized personnel away. Ventilate closed spaces before entering them. Use personal protective equipment. See Section 8 of the SDS for Personal Protective Equipment.

**Methods and material for containment and cleaning up:** Sweep up and place in a clearly labeled container for chemical waste. Avoid dust formation. Clean surface thoroughly to remove residual contamination.

**Notification Procedures:** Prevent entry into waterways, sewer, basements or confined areas. Inform authorities if large amounts are involved.

**Environmental Precautions:** Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

## 7. Handling and storage

<b>Precautions for safe handling:</b>	Use personal protective equipment as required. Avoid contact with eyes, skin, and clothing. Avoid inhalation of dust. Wash thoroughly after handling.
<b>Conditions for safe storage, including any incompatibilities:</b>	Keep containers tightly closed. Store in cool, dry place. Store in a well-ventilated place.

## 8. Exposure controls/personal protection

### Control Parameters

#### Occupational Exposure Limits

None of the components have assigned exposure limits.

#### Appropriate Engineering Controls

No data available.

### Individual protection measures, such as personal protective equipment

<b>General information:</b>	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.
<b>Eye/face protection:</b>	Use tight fitting goggles if dust is generated.
<b>Skin Protection</b>	
<b>Hand Protection:</b>	Wear protective gloves.
<b>Other:</b>	Wear suitable protective clothing.
<b>Respiratory Protection:</b>	In case of inadequate ventilation use suitable respirator.
<b>Hygiene measures:</b>	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Provide eyewash station and safety shower.

## 9. Physical and chemical properties

### Appearance

<b>Physical state:</b>	Solid
<b>Form:</b>	Crystalline solid
<b>Color:</b>	Colorless
<b>Odor:</b>	Odorless
<b>Odor threshold:</b>	No data available.
<b>pH:</b>	No data available.
<b>Melting point/freezing point:</b>	48 °C
<b>Initial boiling point and boiling range:</b>	No data available.
<b>Flash Point:</b>	No data available.
<b>Evaporation rate:</b>	No data available.
<b>Flammability (solid, gas):</b>	No data available.
<b>Upper/lower limit on flammability or explosive limits</b>	
<b>Flammability limit - upper (%):</b>	No data available.

<b>Flammability limit - lower (%):</b>	No data available.
<b>Explosive limit - upper (%):</b>	No data available.
<b>Explosive limit - lower (%):</b>	No data available.
<b>Vapor pressure:</b>	No data available.
<b>Vapor density:</b>	No data available.
<b>Relative density:</b>	1.75 (20 °C)
<b>Solubility(ies)</b>	
<b>Solubility in water:</b>	Soluble
<b>Solubility (other):</b>	No data available.
<b>Partition coefficient (n-octanol/water):</b>	No data available.
<b>Auto-ignition temperature:</b>	No data available.
<b>Decomposition temperature:</b>	No data available.
<b>Viscosity:</b>	No data available.
<b>Other information</b>	
<b>Molecular weight:</b>	248.19 g/mol (H <sub>2</sub> O <sub>3</sub> S <sub>2</sub> .5H <sub>2</sub> O.2Na)

## 10. Stability and reactivity

<b>Reactivity:</b>	No dangerous reaction known under conditions of normal use.
<b>Chemical Stability:</b>	The substance is hygroscopic and will absorb water by contact with the moisture in the air.
<b>Possibility of Hazardous Reactions:</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid:</b>	Contact with air. Moisture.
<b>Incompatible Materials:</b>	Strong oxidizing agents. Strong acids. Strong bases.
<b>Hazardous Decomposition Products:</b>	Carbon dioxide Oxides of sulfur. Sodium oxides

## 11. Toxicological information

### Information on likely routes of exposure

<b>Ingestion:</b>	May cause irritation of the gastrointestinal tract.
<b>Inhalation:</b>	May cause irritation to the respiratory system.
<b>Skin Contact:</b>	May cause irritation.
<b>Eye contact:</b>	May cause temporary eye irritation.

### Information on toxicological effects

#### Acute toxicity (list all possible routes of exposure)

<b>Oral Product:</b>	No data available.
<b>Dermal Product:</b>	No data available.
<b>Inhalation Product:</b>	No data available.
<b>Repeated Dose Toxicity Product:</b>	No data available.

**Skin Corrosion/Irritation**

**Product:** May cause skin irritation.

**Serious Eye Damage/Eye Irritation**

**Product:** May irritate eyes.

**Respiratory or Skin Sensitization**

**Product:** Not a skin sensitizer.

**Carcinogenicity**

**Product:** This substance has no evidence of carcinogenic properties.

**IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:**

No carcinogenic components identified

**US. National Toxicology Program (NTP) Report on Carcinogens:**

No carcinogenic components identified

**US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):**

No carcinogenic components identified

**Germ Cell Mutagenicity**

**In vitro**

**Product:** No mutagenic components identified

**In vivo**

**Product:** No mutagenic components identified

**Reproductive Toxicity**

**Product:** No components toxic to reproduction

**Specific Target Organ Toxicity - Single Exposure**

**Product:** No data available.

**Specific Target Organ Toxicity - Repeated Exposure**

**Product:** No data available.

**Aspiration Hazard**

**Product:** Not classified

**Other Effects:** None known.

<b>12. Ecological information</b>
-----------------------------------

**Ecotoxicity:**

**Acute hazards to the aquatic environment:**

**Fish**

**Product:** No data available.

**Aquatic Invertebrates**

**Product:** No data available.

**Chronic hazards to the aquatic environment:**

**Fish**

**Product:** No data available.

**Aquatic Invertebrates**

**Product:** No data available.

**Toxicity to Aquatic Plants**

**Product:** No data available.

**Persistence and Degradability**

**Biodegradation**

**Product:** There are no data on the degradability of this product.

**BOD/COD Ratio**

**Product:** No data available.

**Bioaccumulative Potential**

**Bioconcentration Factor (BCF)**

**Product:** No data available on bioaccumulation.

**Partition Coefficient n-octanol / water (log Kow)**

**Product:** No data available.

**Mobility in Soil:**

The product is water soluble and may spread in water systems.

**Other Adverse Effects:**

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

**13. Disposal considerations**

**Disposal instructions:**

Discharge, treatment, or disposal may be subject to national, state, or local laws.

**Contaminated Packaging:**

Since emptied containers retain product residue, follow label warnings even after container is emptied.

**14. Transport information**

**DOT**

Not regulated.

**IMDG**

Not regulated.

**IATA**

Not regulated.

**15. Regulatory information**

**US Federal Regulations**

**TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)**

**US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)**

None present or none present in regulated quantities.

**CERCLA Hazardous Substance List (40 CFR 302.4):**

None present or none present in regulated quantities.

**Superfund Amendments and Reauthorization Act of 1986 (SARA)**

**Hazard categories**

Not listed.

**SARA 302 Extremely Hazardous Substance**

None present or none present in regulated quantities.

**SARA 304 Emergency Release Notification**

None present or none present in regulated quantities.

**SARA 311/312 Hazardous Chemical**

None present or none present in regulated quantities.

**SARA 313 (TRI Reporting)**

None present or none present in regulated quantities.

**Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3)**

None present or none present in regulated quantities.

**Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):**

None present or none present in regulated quantities.

**US State Regulations**

**US. California Proposition 65**

No ingredient regulated by CA Prop 65 present.

**US. New Jersey Worker and Community Right-to-Know Act**

No ingredient regulated by NJ Right-to-Know Law present.

**US. Massachusetts RTK - Substance List**

No ingredient regulated by MA Right-to-Know Law present.

**US. Pennsylvania RTK - Hazardous Substances**

No ingredient regulated by PA Right-to-Know Law present.

**US. Rhode Island RTK**



No ingredient regulated by RI Right-to-Know Law present.

**Inventory Status:**

Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
EINECS, ELINCS or NLP:	Not in compliance with the inventory.
Japan (ENCS) List:	On or in compliance with the inventory
China Inv. Existing Chemical Substances:	Not in compliance with the inventory.
Korea Existing Chemicals Inv. (KECI):	Not in compliance with the inventory.
Canada NDSL Inventory:	Not in compliance with the inventory.
Philippines PICCS:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	On or in compliance with the inventory
Japan ISHL Listing:	On or in compliance with the inventory
Japan Pharmacopoeia Listing:	Not in compliance with the inventory.

**16. Other information, including date of preparation or last revision**

**NFPA Hazard ID**



Special hazard.

Hazard rating: 0 - Minimal; 1 - Slight; 2 - Moderate; 3 - Serious; 4 - Severe

**Issue Date:** 03-10-2015**Revision Date:** No data available.**Version #:** 1.2**Further Information:** No data available.

**Disclaimer:** THE INFORMATION PRESENTED IN THIS MATERIAL SAFETY DATA SHEET (MSDS/SDS) WAS PREPARED BY TECHNICAL PERSONNEL BASED ON DATA THAT THEY BELIEVE IN THEIR GOOD FAITH JUDGMENT IS ACCURATE. HOWEVER, THE INFORMATION PROVIDED HEREIN IS PROVIDED "AS IS," AND AVANTOR PERFORMANCE MATERIALS MAKES AND GIVES NO REPRESENTATIONS OR WARRANTIES WHATSOEVER, AND EXPRESSLY DISCLAIMS ALL WARRANTIES REGARDING SUCH INFORMATION AND THE PRODUCT TO WHICH IT RELATES, WHETHER EXPRESS, IMPLIED, OR STATUTORY, INCLUDING WITHOUT LIMITATION<(,<)> WARRANTIES OF ACCURACY, COMPLETENESS, MERCHANTABILITY, NON-INFRINGEMENT, PERFORMANCE, SAFETY, SUITABILITY, STABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, AND ANY WARRANTIES ARISING FROM COURSE OF DEALING, COURSE OF PERFORMANCE, OR USAGE OF TRADE. THIS MSDS/SDS IS INTENDED ONLY AS A GUIDE TO THE APPROPRIATE PRECAUTIONARY HANDLING OF THE MATERIAL BY A PROPERLY TRAINED PERSON USING THIS PRODUCT, AND IS NOT INTENDED TO BE COMPREHENSIVE AS TO THE MANNER AND CONDITIONS OF USE, HANDLING, STORAGE, OR DISPOSAL OF THE PRODUCT. INDIVIDUALS RECEIVING THIS MSDS/SDS MUST ALWAYS EXERCISE THEIR OWN INDEPENDENT JUDGMENT IN DETERMINING THE APPROPRIATENESS OF SUCH ISSUES. ACCORDINGLY, AVANTOR PERFORMANCE MATERIALS ASSUMES NO LIABILITY WHATSOEVER FOR THE USE OF OR RELIANCE UPON THIS INFORMATION. NO SUGGESTIONS FOR USE ARE INTENDED AS, AND NOTHING HEREIN SHALL BE CONSTRUED AS, A RECOMMENDATION TO INFRINGE ANY EXISTING PATENTS OR TO VIOLATE ANY FEDERAL, STATE, LOCAL, OR FOREIGN LAWS. AVANTOR PERFORMANCE MATERIALS REMINDS YOU THAT IT IS YOUR LEGAL DUTY TO MAKE ALL INFORMATION IN THIS MSDS/SDS AVAILABLE TO YOUR EMPLOYEES.