Safety Data Sheet

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision date: 04.05.2018	*Version: 6.0*	*Print date: 04.05.2018*

SECTION 1: Identification

Product identifier

Trade name/designation:	Dimethyl sulfoxide HiPerSolv CHROMANORM® HPLC grade
Product No.:	BDH67001
Synonymes:	no data available
CAS No.:	67-68-5
Other means of identification:	

Relevant identified uses of the substance or mixture and uses advised against

Recommended Use:	For Further Manufacturing Use Only
Uses advised against:	Not for Human or Animal Drug Use

Details of the supplier of the safety data sheet

Supplier

VWR International LLC

Street	100 Matsonford Road Radnor Corporate Center, Building One, Suite 200 P. O. Box 6660
Postal code/city	Radnor, PA 19087
Telephone	+1-800-932-5000 toll-free within US/Canada +1-610-386-1700
Telefax:	+1-610-728-2103

Emergency telephone

Telephone +1-800-424-9300 (Chemtrec, 24 hrs/day, 7 days/week, USA)

Preparation Information

VWR International - Product Information Compliance

E-mail sds@vwr.com

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

GHS Classification in accordance with 29 CFR 1910.1200 (OSHA HCS)

Hazard classes and hazard categories	Hazard statements
Flammable liquid, category 4	H227
Eye irritation, category 2	H319
Skin irritation, category 2	H315

2.2 Label elements

Labelling in accordance with 29 CFR 1910.1200 (OSHA HCS)

Hazard pictograms



Signal word: Warning

Hazard statements	
H227	Combustible liquid
H319	Causes serious eye irritation.
H315	Causes skin irritation.

Precautionary statements	
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P243	Take precautionary measures against static discharge.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P302+P352	IF ON SKIN: Wash with plenty of water/…
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308+P311	IF exposed or concerned: Call a POISON CENTER/doctor/…
P403+P235	Store in a well-ventilated place. Keep cool.

Hazards not otherwise classified (HNOC)

none/none

SECTION 3: Composition / information on ingredients

3.1 Substances

Substance name	Dimethyl sulfoxide
Molecular formula	(CH3)2SO
Molecular weight	78.14 g/mol
CAS No.	67-68-5

SECTION 4: First aid measures

4.1 General information

When in doubt or if symptoms are observed, get medical advice. If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

After inhalation

Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration. In case of respiratory tract irritation, consult a physician.

In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

In case of ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

4.2 Most important symptoms/effects, acute and delayed

no data available

4.3 Indication of any immediate medical attention and special treatment needed

no data available

4.4 Self-protection of the first aider

First aider: Pay attention to self-protection!

4.5 Information to physician

no data available

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

The product itself does not burn.
Co-ordinate fire-fighting measures to the fire surroundings.

Extinguishing media which must not be used for safety reasons

no restriction

5.2 Specific hazards arising from the chemical

In case of fire may be liberated:
Carbon monoxide
Carbon dioxide (CO2)
Sulphur oxides

5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives.

Protective equipment and precautions for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Do not allow run-off from fire-fighting to enter drains or water courses.

Do not inhale explosion and combustion gases.

Use water spray/stream to protect personnel and to cool endangered containers.

In case of fire: Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety.

6.2 Environmental precautions

Discharge into the environment must be avoided.

6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Collect in closed and suitable containers for disposal.

6.4 Additional information

Clear spills immediately.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Avoid: Inhalation Avoid contact with eyes and skin. Use extractor hood (laboratory). If handled uncovered, arrangements with local exhaust ventilation have to be used. If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means. Protect from moisture.

7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: Ambient temperature

Keep container tightly closed and in a well-ventilated place.

7.3 Specific end use(s)

no data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

8.2 Engineering controls

Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

Personal protection equipment (PPE)

Wear suitable protective clothing. When handling with chemical substances, protective clothing must be worn.

Eye/face protection

Eye glasses with side protection

Skin protection

Wear suitable gloves. When handling with chemical substances, protective gloves must be worn. In the case of wanting to use the gloves again, clean them before taking off and air them well. Check leak tightness/impermeability prior to use.

By short-term hand contact

Suitable material:	CR (polychloroprene, chloroprene rubber)
Thickness of the glove material:	0,13 mm
Breakthrough time (maximum wearing time):	10 min

By long-term hand contact

Suitable material:	CR (polychloroprene, chloroprene rubber)
Thickness of the glove material:	-
Breakthrough time (maximum wearing time):	> 480 min

Respiratory protection

Usually no personal respirative protection necessary.

Additional information

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

Environmental exposure controls

no data available

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	liquid
Color:	colorless
(b) Odour:	no data available
(c) Odour threshold:	no data available

Safety relevant basic data

(d) pH:	no data available
(e) Melting point/freezing point:	18.5 °C
(f) Initial boiling point and boiling range:	189 °C (1013 hPa)
(g) Flash point:	87 °C
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	Combustible liquid
(j) Flammability or explosive limits	
Lower explosion limit:	1.8 % (v/v)
Upper explosion limit:	63 % (v/v)
(k) Vapour pressure:	0.6 hPa (20 °C)
(l) Vapour density:	2.7 (20 °C)
(m) Relative density:	1.101 g/cm³ (20 °C)
(n) Solubility(ies)	
Water solubility (g/L):	1,000 g/l (20 °C)
Soluble (g/L) in Ethanol:	no data available
(o) Partition coefficient: n-octanol/water:	-2.03 (20 °C)
(p) Auto-ignition temperature:	300-302 °C
(q) Decomposition temperature:	no data available
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	2.14 mPa*s (20 °C)
(s) Explosive properties:	not applicable
(t) Oxidising properties:	not applicable

9.2 Other information

Bulk density:	not applicable
Refraction index:	1.4783 (589 nm; 20 °C)
Dissociation constant:	no data available
Surface tension:	no data available
Henry constant:	no data available

SECTION 10: Stability and reactivity

10.1 Reactivity

no data available

10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

no data available

10.6 Hazardous decomposition products

no data available

10.7 Additional information

no data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute effects

Acute oral toxicity:
LD50: > 14500 mg/kg - Rat - (RTECS)

Acute dermal toxicity:
LD50: > 40000 mg/kg - Rat - (RTECS)

Acute inhalation toxicity:
no data available

Irritant and corrosive effects

Primary irritation to the skin:
Causes skin irritation.

Irritation to eyes:
Causes serious eye irritation.

Irritation to respiratory tract:
not applicable

Respiratory or skin sensitization

In case of skin contact: not sensitising
After inhalation: not sensitising

STOT-single exposure

not applicable

STOT-repeated exposure

not applicable

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

Carcinogenicity

The table below indicates whether each agency has listed any ingredient as a carcinogen.

no data available	ACGIH	IARC	NTP	OSHA

Germ cell mutagenicity

No indications of human germ cell mutagenicity exist.

Reproductive toxicity

No indications of human reproductive toxicity exist.

Aspiration hazard

not applicable

Other adverse effects

no data available

Additional information

no data available

SECTION 12: Ecological information

12.1 Ecotoxicity

Fish toxicity:

LC50: 36200 mg/l (96 h) - Geiger, D.L., L.T. Brooke, and D.J. Call 1990. Acute Toxicities of Organic Chemicals to Fathead Minnows (Pimephales promelas), Volume 5

Daphnia toxicity:

LC50: 25000 mg/l (48 h) - Goto, T., and J. Hiromi 2003. Toxicity of 17alpha-Ethynylestradiol and Norethindrone, Constituents of an Oral Contraceptive Pill to the Swimming and Reproduction of Cladoceran Daphnia magna, with Special Reference to Their Synergetic Effect

Algae toxicity:

no data available

Bacteria toxicity:

no data available

12.2 Persistence and degradability

no data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: -2.03 (20 °C)

12.4 Mobility in soil:

no data available

12.5 Results of PBT/vPvB assessment

no data available

12.6 Other adverse effects

no data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Appropriate disposal / Product

Dispose according to legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: 160508

Appropriate disposal / Package

Dispose according to legislation. Handle contaminated packages in the same way as the substance itself.

Additional information

no data available

SECTION 14: Transport information

Land transport (DOT)

No dangerous good in sense of this transport regulation.

Sea transport (IMDG)

No dangerous good in sense of this transport regulation.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code
not relevant

Air transport (ICAO-TI / IATA-DGR)

No dangerous good in sense of this transport regulation.

SECTION 15: Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture

SARA 313 Components

Not listed.

Massachusetts Right To Know Components

Not listed.

Pennsylvania Right To Know Components

Not listed.

New Jersey Right To Know Components

Listed

California Prop. 65 Components

Not listed.

SECTION 16: Other information

Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygiensts
DOT - Department of Transportation
IARC - International Agency for Research on Cancer
IATA-DGR - International Air Transport Association-Dangerous Goods Regulations
ICAO-TI - International Civil Aviation Organization-Technical Instructions
IMDG - International Maritime Code for Dangerous Goods
LTV - Long Term Value
NIOSH - National Institute for Occupational Safety and Health
NTP - National Toxicology Program
OSHA - Occupational Safety & Health Administration
PBT - Persistent, Bioaccumulative and Toxic
PEL - Permissible Exposure Limit
STV - Short Term Value
SVHC - Substances of Very High Concern
TDG - Transport of Dangerous Goods
TLV - Threshold Limit Value
vPvB - very Persistent, very Bioaccumulative

Additional information

Indication of changes: none/none

The above information is believed to be correct but does not purport to be all-inclusive and shall be used only as a guidance. The information in this document is based on the present state knowledge and is applicable to the product with regard to appropriate safty precautions. It does not represent any guarantee of the properties of the product. VWR International and his Affiliates shall not be held liable for any damage resulting from handling.