

Printing date 01/11/2006

Reviewed on 08/12/2003

1 Identification of substance:

· Product name: Enterococcosel Agar

· Catalog number: 221492

· Manufacturer/Supplier:

BD Diagnostic Systems

7 Loveton Circle

Sparks, MD 21152

Tel: (410) 771-0100 or (800) 638-8663

- · Information department: Technical Services
- · Emergency information:

In case of a chemical emergency, spill, fire, exposure, or accident contact BD Diagnostic Systems at (410)771-0100 or (800)638-8663, or ChemTrec at (800)424-9300.

2 Composition/Data on components:

- · Chemical characterization:
- · CAS No. Description:

Not applicable

- · Chemical characterization
- · Description: Mixture consisting of the following components.

· Dangerous components:				
26628-22-8	sodium azide	0.44%		
	bile salts No. 3	7.93%		

3 Hazards identification

· Hazard description:



Xn Harmful

· Information pertaining to particular dangers for man and environment

R 22 Harmful if swallowed.

R 36/37/38 Irritating to eyes, respiratory system and skin.

R 52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment

· Classification system

The classification was made according to the latest editions of international substances lists, and expanded upon from company and literature data.

· NFPA ratings (scale 0-4)



Health = 3 Fire = 0Reactivity = 0

USA



Printing date 01/11/2006 Reviewed on 08/12/2003

Product name: Enterococcosel Agar

(Contd. of page 1)

4 First aid measures

- · General information No special measures required.
- · After inhalation Supply fresh air; consult doctor in case of complaints.
- · After skin contact Immediately wash with water and soap and rinse thoroughly.
- · After eye contact Rinse opened eye for 15 minutes under running water. Then consult a doctor.
- · After swallowing If symptoms persist consult doctor.

5 Fire fighting measures

· Suitable extinguishing agents

CO2, ABC multipurpose dry chemical or water spray. Fight larger fires with water spray or alcohol resistant foam.

· Special hazards caused by the material, its products of combustion or resulting gases:

During heating or in case of fire toxic gases may be produced.

Nitrogen oxides (NOx)

· Protective equipment: No special measures required.

6 Accidental release measures

- · Person-related safety precautions: Not required.
- · Measures for environmental protection: Wipe up with damp sponge or mop.
- · Measures for cleaning/collecting: No special measures required.
- · Additional information:

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

7 Handling and storage

- · Handling
- · Information for safe handling: No special measures required.
- · Information about protection against explosions and fires: No special measures required.
- · Storage
- Requirements to be met by storerooms and receptacles: 2 25 C
- · Information about storage in one common storage facility:

Do not store together with oxidizing and acidic materials as well as heavy-metal compounds.

· Further information about storage conditions: Store in cool, dry conditions in well sealed containers.

8 Exposure controls and personal protection

· Additional information about design of technical systems: No further data; see item 7.

(Contd. on page 3)



Printing date 01/11/2006 Reviewed on 08/12/2003

Product name: Enterococcosel Agar

(Contd. of page 2)

· Components with limit values that require monitoring at the workplace:

26628-22-8 sodium azide

REL Short-term value: C 0.3** mg/m³, C 0.1* ppm

*as HN3 vapor; **as NaN3

TLV Short-term value: C 0.29** mg/m³, C 0.11* ppm

*as HN3 vapor; **as NaN3

- \cdot Additional information: The lists that were valid during the creation were used as basis.
- · Personal Protective Equipment
- · General protective and hygienic measures

The usual precautionary measures for handling chemicals should be followed.

· Breathing equipment:

In case of brief exposure, use a chemical fume hood or a NIOSH/MSHA-approved respirator.

· Protection of hands:





Chemical resistant gloves (i.e. nitrile, or equivalent).

- · Eve protection: Safety glasses
- · **Body protection:** Protective work clothing (lab coat).

9 Physical and chemical properties:

· General Information				
Form:	Solid.			
Color:	Yellow-brown			
Odor:	Characteristic			
· Change in condition	Undetermined			
· Melting point/Melting range:	Not determined			
Boiling point/Boiling range:	Not determined			
· Flash point:	Not applicable			
· Flammability (solid, gaseous) Product is not flammable.				
Danger of explosion:	Forms very sensitive explosive metallic compounds.			
Density:	Not determined			
· Solubility in / Miscibility with				
Water:	Insoluble			
· Solvent content:				
· Solids content:	100.0 %			

10 Stability and reactivity

• Thermal decomposition / conditions to be avoided: No decomposition if used according to specifications.

(Contd. on page 4)



Printing date 01/11/2006 Reviewed on 08/12/2003

Product name: Enterococcosel Agar

(Contd. of page 3)

· Materials to be avoided:

Incompatible materials: acidic material and metals

Incompatible material: strong oxidizers.

- · Dangerous reactions No dangerous reactions known
- · Dangerous products of decomposition: Chlorine (Cl)
- · Additional information:

Sodium azide is present in this product. Contact with acidic solutions and metal compounds over time may form potentially explosive metal azides. Should any of this material be introduced into a sanitary sewer system, flush with copious amounts of water.

11 Toxicological information

- · Acute toxicity:
- · LD/LC50 values that are relevant for classification:

26628-22-8 sodium azide

Oral LD50 27 mg/kg (rat)

- · Primary irritant effect:
- · on the skin: Irritant to skin and mucous membranes.
- · on the eye: Irritating effect.
- · Sensitization: No sensitizing effects known.
- · Subacute to chronic toxicity: Target organs: respiratory tract, eyes, kidneys, and skin.
- · Additional toxicological information:

Harmful

The product shows the following dangers according to internally approved calculation methods for preparations:

12 Ecological information:

- · Ecotoxical effects:
- Other information:

The ecological effects have not been thoroughly investigated, but currently none have been identified.

· General notes: Water hazard class 1 (Self-assessment): slightly hazardous for water.

13 Disposal considerations

- · Product:
- · Recommendation

Smaller quantities can be disposed of with solid waste.

Dispose of material in accordance with federal (40 CFR 261.3), state and local requirements.

This product is not considered a RCRA hazardous waste.

- · Uncleaned packagings:
- · Recommendation: Disposal must be made according to state and federal regulations.

TC A

(Contd. on page 5)



Printing date 01/11/2006 Reviewed on 08/12/2003

Product name: Enterococcosel Agar

(Contd. of page 4)

14 Transport information

- · DOT regulations:
- · Hazard class:
- · Land transport ADR/RID (cross-border)
- · ADR/RID class:
- · Maritime transport IMDG:
- · IMDG Class:
- · Marine pollutant: No
- · Air transport ICAO-TI and IATA-DGR:
- · ICAO/IATA Class: -

7 /	T	7 .	
	POOT	Ilatio	700
	14341	ılatio	

- · SARA Section 355 (extremely hazardous substances)
- 26628-22-8 sodium azide
- · SARA Section 313 (specific toxic chemical listings)
- 26628-22-8 sodium azide
- · TSCA (Toxic Substances Control Act)
- 9002-18-0 agar
 - 8013-01-2 yeast extract
 - 531-75-9 esculin
 - 68-04-2 Sodium citrate
 - 497-19-8 sodium carbonate
- 1185-57-5 ferric ammonium citrate
- 26628-22-8 sodium azide
- · California Proposition 65 Chemicals known to cause cancer
- None of the ingredients is listed.
- · California Proposition 65 Chemicals known to cause reproductive toxicity for females:
- None of the ingredients is listed.
- · California Proposition 65 Chemicals known to cause reproductive toxicity for males:
- None of the ingredients is listed.
- · California Proposition 65 Chemicals known to cause developmental toxicity:
- None of the ingredients is listed.
- · Carcinogenicity categories
- · IARC (International Agency for Research on Cancer)
 - None of the ingredients is listed.
- · NTP (National Toxicology Program)
- None of the ingredients is listed.
- · TLV (Threshold Limit Value established by ACGIH)
 - 26628-22-8 *sodium azide*

A4

(Contd. on page 6)



Printing date 01/11/2006 Reviewed on 08/12/2003

Product name: Enterococcosel Agar

(Contd. of page 5)

· Product related hazard information:

Observe the general safety regulations when handling chemicals

The product has been classified and marked in accordance with regulations on hazardous materials.

· Hazard symbols:

Xn Harmful

· Hazard-determining components of labeling:

sodium azide

bile salts No. 3

· Risk phrases:

22 Harmful if swallowed.

36/37/38 Irritating to eyes, respiratory system and skin.

52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment

· Safety phrases:

- 2 Keep out of the reach of children.
- 13 Keep away from food, drink and animal feedingstuffs.
- 22 Do not breathe dust.
- 36 Wear suitable protective clothing.
- 46 If swallowed, seek medical advice immediately and show this container or label.

16 Other information:

To the best of our knowledge, the information contained herein is accurate. However, neither Becton, Dickinson and Company or any of its subsidiaries assumes any liabilities whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

- · Department issuing MSDS: Safety and Environment Department
- · Contact: Technical Service Representative

USA