



Item Number C1679

Item Microcrystalline Cellulose, NF

CAS Number 9004-34-6

Molecular Formula

Molecular Weight

Degree of Polymerization.....Max. 350

pH of Solution..... 5.0-7.5

Bulk Density..... To pass test

MAXIMUM LIMITS

Conductivity..... 75 μ S/cm

Loss on Drying..... 7.0%

Residue on Ignition..... 0.1%

Water-Soluble Substances.....0.25%

Ether-Soluble Substances.....0.05%

Heavy Metals.....0.001%

Residual Solvents.....To pass test

Microbial Limits:

Total Aerobic Microbial Count..... 1,000 cfu

Total Combined Molds and Yeasts Count.....100 cfu

Staphylococcus Aureus.....To pass test

Pseudomonas Aeruginosa.....To pass test

Escherichia coli.....To pass test

Salmonella.....To pass test

Spectrum Chemicals & Laboratory Products

Corporate Headquarters: East Coast Facility:

14422 S. San Pedro St. 755 Jersey Ave.

Gardena, CA 90248 New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843