


TSN Antibody (Center)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP12376c	WB, IHC, E	H	NP_004613.1 , Q15631
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB31284

Application Data:

Calculated MW: 26183 Da



TSN Antibody (Center) (Cat. #AP12376c) western blot analysis in HeLa cell line lysates (35ug/lane). This demonstrates the TSN antibody detected the TSN protein (arrow).



TSN Antibody (Center) (Cat. #AP12376c) immunohistochemistry analysis in formalin fixed and paraffin embedded human brain tissue followed by peroxidase conjugation of the secondary antibody and DAB staining. This data demonstrates the use of TSN Antibody (Center) for immunohistochemistry. Clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
7247	TSN

Other Names:

TSN;Translin;

Target/Specificity:

This TSN antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 116-146 amino acids from the Central region of human TSN.

Application Notes:

The suggested dilution is:
 ELISA 1:1,000

Western blotting 1:100~500
Immunohistochemistry 1:10~50

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

TSN Antibody (Center) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

TSN Antibody (Center) is for research use only and not for use in diagnostic or therapeutic procedures.
