


TPRX1 Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP16916a	WB, E	H	NP_940881.2 , Q8N7U7
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB36103

Application Data: Calculated MW: 40603 Da



TPRX1 Antibody (N-term) (Cat. #AP16916a) western blot analysis in A2058 cell line lysates (35ug/lane). This demonstrates the TPRX1 antibody detected the TPRX1 protein (arrow).

Gene ID:	Gene Symbol:
284355	TPRX1

Other Names:

Tetra-peptide repeat homeobox protein 1;TPRX1;

Target/Specificity:

This TPRX1 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 1-30 amino acids from the N-terminal region of human TPRX1.

Application Notes:

The suggested dilution is:
 ELISA 1:1,000
 Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

TPRX1 Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage,

place the at -20°C.

Precautions:

TPRX1 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
