


## RGS5 Antibody (N-term)

### Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

<b>Catalog #</b>	<b>Applications:</b>	<b>Reactivity:</b>	<b>Accessions:</b>
AP14899a	WB, E	H	<a href="#">O15539</a> , <a href="#">NP_003608.1</a>
<b>Concentration:</b>	<b>Size:</b>	<b>Isotype:</b>	<b>Clone Name:</b>
0.25 mg/ml	0.1 mg	Rabbit Ig	RB35222

#### Application Data: Calculated MW: 20946 Da



RGS5 Antibody (N-term) (Cat. #AP14899a) western blot analysis in CEM cell line lysates (35ug/lane). This demonstrates the RGS5 antibody detected the RGS5 protein (arrow).

<b>Gene ID:</b>	<b>Gene Symbol:</b>
<a href="#">8490</a>	RGS5

#### Other Names:

Regulator of G-protein signaling 5;RGS5;

#### Target/Specificity:

This RGS5 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 23-53 amino acids from the N-terminal region of human RGS5.

#### Application Notes:

The suggested dilution is:  
 ELISA 1:1,000  
 Western blotting 1:100~500

#### Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

#### Storage:

RGS5 Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage,

place the at -20&deg;C.

---

**Precautions:**

RGS5 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.

---