


PRR15 Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP14978b	WB, E	H	NP_787083.1 , Q8IV56
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB35119

Application Data: Calculated MW: 13715 Da



PRR15 Antibody (C-term) (Cat. #AP14978b) western blot analysis in NCI-H292 cell line lysates (35ug/lane). This demonstrates the PRR15 antibody detected the PRR15 protein (arrow).

Gene ID:	Gene Symbol:
222171	PRR15

Other Names:

Proline-rich protein 15; PRR15;

Target/Specificity:

This PRR15 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 70-100 amino acids from the C-terminal region of human PRR15.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

PRR15 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place

the at -20°C.

Precautions:

PRR15 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
