


VPS45 Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP16102b	WB, E	H	Q9NRW7 , NP_009190.2
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB34261

Application Data:

Calculated MW: 65077 Da



VPS45 Antibody (C-term) (Cat. #AP16102b) western blot analysis in mouse brain tissue lysates (35ug/lane). This demonstrates the VPS45 antibody detected the VPS45 protein (arrow).

Gene ID:	Gene Symbol:
11311	VPS45

Other Names:

Vacuolar protein sorting-associated protein 45; VPS45; VPS45A; VPS45B

Target/Specificity:

This VPS45 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 460-489 amino acids from the C-terminal region of human VPS45.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

VPS45 Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

VPS45 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
