BNC1 Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP16281a	WB, E	H	Q01954, NP_001708.3

Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB35586

Application Data:

Calculated MW: 110972 Da



BNC1 Antibody (N-term) (Cat. #AP16281a) western blot analysis in HepG2 cell line lysates (35ug/lane).This demonstrates the BNC1 antibody detected the BNC1 protein (arrow).

Gene ID:	Gene Symbol:
646	BNC1

Other Names:

Zinc finger protein basonuclin-1;BNC1;BNC

Target/Specificity:

This BNC1 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 1-30 amino acids from the N-terminal region of human BNC1.

Application Notes:

The suggested dilution is:
ELISA 1:1,000
Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

BNC1 Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage,

place the at -20°C.

Precautions:

BNC1 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.