


Elongin A Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP1918a	WB, E	H, M	Q14241
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB8365

Application Data:

Calculated MW: 87230 Da



Western blot analysis of Elongin A (arrow) using rabbit polyclonal Elongin A Antibody (Cat. #AP1918a). 293 cell lysates (2 ug/lane) either nontransfected (Lane 1) or transiently transfected (Lane 2) with the Elongin A gene.



Elongin A Antibody (Cat. #AP1918a) western blot analysis in mouse NIH-3T3 cell line lysates (35ug/lane). This demonstrates the Elongin A antibody detected the Elongin A protein (arrow).

Gene ID:	Gene Symbol:
6924	TCEB3

Other Names:

Transcription elongation factor B polypeptide 3; RNA polymerase II transcription factor SIII subunit A1; SIII p110; Elongin A; EloA; Elongin 110 kDa subunit; TCEB3;

Target/Specificity:

This Elongin A antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 79~108 amino acids from the N-terminal region of human Elongin A.

Application Notes:

The suggested dilution is:

ELISA 1:1,000
Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

Elongin A Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
