


TMC6 Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP14212a	WB, E	H	Q7Z403 , NP_009198.4 , NP_001120670.1
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB34148

Application Data:

Calculated MW: 90045 Da



TMC6 Antibody (N-term) (Cat. #AP14212a) western blot analysis in A2058 cell line lysates (35ug/lane). This demonstrates the TMC6 antibody detected the TMC6 protein (arrow).

Gene ID:	Gene Symbol:
11322	TMC6

Other Names:

Transmembrane channel-like protein 6;TMC6;EVER1; EVIN1

Target/Specificity:

This TMC6 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 159-188 amino acids from the N-terminal region of human TMC6.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

TMC6 Antibody (N-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

TMC6 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
