


ARNT Antibody (Center V528)

Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP14310c	WB, E	H	P27540 , NP_848514.1 , NP_001659.1
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB00060

Application Data:

Calculated MW: 86636 Da



ARNT Antibody (V528) (Cat. #AP14310c) western blot analysis in NCI-H460 cell line lysates (35ug/lane). This demonstrates the ARNT antibody detected the ARNT protein (arrow).

Gene ID:	Gene Symbol:
405	ARNT

Other Names:

Aryl hydrocarbon receptor nuclear translocator;ARNT;BHLHE2

Target/Specificity:

This ARNT antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 512-544 amino acids from the Central region of human ARNT.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:50~100

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is prepared by Saturated Ammonium Sulfate (SAS) precipitation followed by dialysis against PBS.

Storage:

ARNT Antibody (Center V528) can be refrigerated at 2-8°C for up to 6 months. For long term storage, place the at -20°C.

Precautions:

ARNT Antibody (Center V528) is for research use only and not for use in diagnostic or therapeutic procedures.
