

## RANBP9 Antibody (Center)


### Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP8501c	WB, IHC, FC, E	H	<a href="#">Q96S59</a>


Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB19813

#### Application Data:


**Calculated MW: 77847 Da**



Western blot analysis of RANBP9 Antibody (Center) (Cat. #AP8501c) in MDA-MB231 cell line lysates (35ug/lane). RANBP9 (arrow) was detected using the purified Pab.



Formalin-fixed and paraffin-embedded human skeletal muscle reacted with RANBP9 Antibody (Center), which was peroxidase-conjugated to the secondary antibody, followed by DAB staining. This data demonstrates the use of this antibody for immunohistochemistry; clinical relevance has not been evaluated.



Flow cytometric analysis of MDA-231 cells using RANBP9 Antibody (Center)(bottom histogram) compared to a negative control cell (top histogram). FITC-conjugated goat-anti-rabbit secondary antibodies were used for the analysis.

Gene ID:	Gene Symbol:
<a href="#">10048</a>	RANBP9

#### Other Names:

Ran-binding protein 9; RanBP9; RanBP7; Ran-binding protein M; RanBPM; BPM90; BPM-L

---

**Target/Specificity:**

This RANBP9 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 346~375 amino acids from the Center region of human RANBP9.

---

**Application Notes:**

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:50~100

Immunohistochemistry 1:50~100

Flow cytometric 1:10~50

---

**Format:**

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is prepared by Saturated Ammonium Sulfate (SAS) precipitation followed by dialysis against PBS.

---

**Storage:**

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

---

**Precautions:**

RANBP9 Antibody (Center) is for research use only and not for use in diagnostic or therapeutic procedures.

---