


## PNPO Antibody (C-term)

### Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

<b>Catalog #</b>	<b>Applications:</b>	<b>Reactivity:</b>	<b>Accessions:</b>
AP9393d	WB, E	H	<a href="#">Q9NVS9</a>
<b>Concentration:</b>	<b>Size:</b>	<b>Isotype:</b>	<b>Clone Name:</b>
0.25 mg/ml	0.1 mg	Rabbit Ig	RB23831

#### Application Data:

Calculated MW: 29988 Da



Western blot analysis of PNPO Antibody (C-term) (Cat. #AP9393d) in 293 cell line lysates (35ug/lane). PNPO (arrow) was detected using the purified Pab.

<b>Gene ID:</b>	<b>Gene Symbol:</b>
<a href="#">55163</a>	PNPO

#### Other Names:

Pyridoxamine-phosphate oxidase; Pyridoxine-5'-phosphate oxidase, PNPO

#### Target/Specificity:

This PNPO antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 232~261 amino acids from the C-terminal region of human PNPO.

#### Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

#### Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

#### Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in

small aliquots to prevent freeze-thaw cycles.

---

**Precautions:**

PNPO Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.

---