


## NCOA7 Antibody (N-term)

### Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP9535a	WB, FC, IHC, E	H	<a href="#">Q8NI08</a>

Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB24112


#### Application Data: Calculated MW: 106162 Da



Western blot analysis of NCOA7 Antibody (N-term) (Cat. #AP9535a) in 293, MDA-MB435 cell line lysates (35ug/lane). NCOA7 (arrow) was detected using the purified Pab.



Formalin-fixed and paraffin-embedded human brain tissue reacted with NCOA7 Antibody (N-term), which was peroxidase-conjugated to the secondary antibody, followed by DAB staining. This data demonstrates the use of this antibody for immunohistochemistry; clinical relevance has not been evaluated.



NCOA7 Antibody (N-term) (Cat. #AP9535a) flow cytometric analysis of 293 cells (right histogram) compared to a negative control cell (left histogram). FITC-conjugated goat-anti-rabbit secondary antibodies were used for the analysis.

Gene ID:	Gene Symbol:
<a href="#">135112</a>	NCOA7

#### Other Names:

Estrogen nuclear receptor coactivator 1; 140 kDa estrogen receptor-associated protein; Nuclear receptor coactivator 7; Nbla10993, Nbla00052, ESNA1, ERAP140, NCOA7

---

**Target/Specificity:**

This NCOA7 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 82~112 amino acids from the N-terminal region of human NCOA7.

---

**Application Notes:**

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Immunohistochemistry 1:50~100

Flow cytometric 1:10~50

---

**Format:**

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

---

**Storage:**

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

---

**Precautions:**

NCOA7 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.

---