




VAMP4 Antibody (Center)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP5861c	WB, IHC, E	H, M	O75379 , NP_001172056.1 , NP_003753.2
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB22111
Application Data:	Calculated MW: 16397 Da		
	<p>VAMP4 Antibody (Center) (Cat. #AP5861c) western blot analysis in K562 cell line lysates (35ug/lane).This demonstrates the VAMP4 antibody detected the VAMP4 protein (arrow).</p>		
	<p>VAMP4 Antibody (Center) (Cat. #AP5861c) western blot analysis in mouse liver tissue lysates (35ug/lane).This demonstrates the VAMP4 antibody detected the VAMP4 protein (arrow).</p>		
	<p>VAMP4 antibody (Center) (Cat. #AP5861c) immunohistochemistry analysis in formalin fixed and paraffin embedded human hepatocarcinoma followed by peroxidase conjugation of the secondary antibody and DAB staining. This data demonstrates the use of the VAMP4 antibody (Center) for immunohistochemistry. Clinical relevance has not been evaluated.</p>		
Gene ID:	Gene Symbol:		
8674	VAMP4		

Other Names:

VAMP4;

Target/Specificity:

This VAMP4 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 23-53 amino acids from the Central region of human VAMP4.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Immunohistochemistry 1:50~100

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

This product is for research use only. Not for use in diagnostic or therapeutic procedures.
